



RoadFlair

BRP390 LED81/NW 57W 220-240V DM

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

General Information	
Lamp colour code	740 neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC-MLO [Polycarbonate micro lens optic]
Control interface	-
Connection	Mains outlet socket
Cable	Cable 0.5 m without plug
Protection class IEC	Safety class I (I)
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	-
Constant light output	No
LED engine type	LED

Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-

Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 or 60 Hz
Power factor (min.)	0.9

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Aluminum die-cast
Optical cover/lens material	Polycarbonate
Mounting device	48/60S [Side-entry for diameter 48-60 mm]
Optical cover/lens shape	Ball, globular
Optical cover/lens finish	Frosted
Overall length	402 mm
Overall width	156 mm
Overall height	85 mm
Colour	Grey

RoadFlair

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	8123 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>70
Initial chromaticity	5 SDCM
Initial input power	57 W
Power consumption tolerance	+/-10%

Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	911401861398
Order product name	BRP390 LED81/NW 57W 220-240V DM
Order code	01861398
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401861398
Net weight (piece)	2.799 kg



Dimensional drawing



BRP391/392/393/394 RoadFlair

