



RoadFlair

BRP394 LED412/NW 285W 220-240V DM PSR

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

| General Information | |
|--------------------------------|--|
| Lamp colour code | 740 neutral white |
| Light source replaceable | No |
| Driver included | Yes |
| Optical cover/lens type | PC-MLO [Polycarbonate micro lens optic] |
| Control interface | Analog |
| Connection | Mains outlet socket |
| Cable | - |
| Protection class IEC | Safety class I (I) |
| Flammability mark | NO [-] |
| CE mark | CE mark |
| ENEC mark | - |
| LED engine type | LED |
| Light Technical | |
| Standard tilt angle post-top | - |
| Standard tilt angle side entry | - |

| Operating and Electrical | |
|-----------------------------|--|
| Input voltage | 220 to 240 V |
| Input frequency | 50 or 60 Hz |
| Power factor (min.) | 0.9 |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Housing material | Aluminum die-cast |
| Optical cover/lens material | Polycarbonate |
| Mounting device | 48/60S [Side-entry for diameter 48-60 mm] |
| Optical cover/lens shape | Ball, globular |
| Optical cover/lens finish | Frosted |
| Overall length | 870 mm |
| Overall width | 295 mm |
| Overall height | 86 mm |
| Colour | Grey |

RoadFlair

Approval and Application

| | |
|------------------------------|---|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |

Initial Performance (IEC Compliant)

| | |
|--------------------------------|----------|
| Initial luminous flux | 41243 lm |
| Luminous flux tolerance | +/-10% |
| Initial LED luminaire efficacy | 140 lm/W |
| Lamp colour temperature | 4000 K |
| Colour Rendering Index | >70 |
| Initial chromaticity | 30 SDCM |
| Initial input power | 285 W |
| Power consumption tolerance | +/-10% |


Application Conditions

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|


| | |
|-----------------------|-----|
| Maximum dimming level | 10% |
|-----------------------|-----|

Product Data

| | |
|---------------------------------|---------------------------------------|
| Full product code | 911401864498 |
| Order product name | BRP394 LED412/NW 285W 220-240V DM PSR |
| Order code | 01864498 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| Material no. (12NC) | 911401864498 |
| Net weight (piece) | 9.999 kg |



Dimensional drawing



BRP391/392/393/394 RoadFlair

