



RoadFlair

BRP394 LED410/WW 308W 220-240V DM PSR

RoadFlair, 41008 lm, 308 W, 730 warm white, Analog, Safety class I, Side-entry for diameter 48 to 60 mm

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

General Information		Light source color	
Light source replaceable	No	730 warm white	
Driver included	Yes	Optical cover type	
Light source engine type	LED	Polycarbonate micro lens optic	
Flammability mark	For mounting on normally flammable surfaces	Operating and Electrical	
CE mark	CE mark	Input Voltage	220 to 240 V
ENEC mark	-	Line Frequency	50 or 60 Hz
Light Technical		Power Consumption	308 W
Luminous Flux	41,008 lm	Power Factor (Fraction)	0.9
Standard tilt angle posttop	-	Connection	Mains outlet socket
Standard tilt angle side entry	-	Cable	-
Correlated Color Temperature (Nom)	3000 K	Temperature	
Luminous Efficacy (rated) (Nom)	140 lm/W	Ambient temperature range	
Color rendering index (CRI)	>70	-40 to +50 °C	

RoadFlair

Controls and Dimming

Dimmable	Yes
Control interface	Analog

Mechanical and Housing

Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Gray
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Ball, globular
Optical cover finish	Frosted
Overall length	870 mm
Overall width	295 mm
Overall height	86 mm
Effective projected area	0.25 m ²
Dimensions (Height x Width x Depth)	86 x 295 x 870 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class I
----------------------	----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM < 5
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BRP394 LED410/WW 308W 220-240V DM PSR
Full product name	BRP394 LED410/WW 308W 220-240V DM PSR
Full product code	911401868098
Order code	911401868098
Material Nr. (12NC)	911401868098
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

