



GreenVision Xceed Gen2

BRP381 LED133/NW 95W 220-240V DM PSR

GreenVision Xceed Gen2, 13300 lm, 95 W, 740 neutral white, Analog, Safety class I

Sustainability, citizen well-being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving these goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads and streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, roadways and rural areas – our luminaires provide optimal light for all application areas. Additionally, the GreenVision Xceed Gen2 is ready to be connected to, and work with, smart city ecosystems. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

Product data

General Information			
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	140 lm/W
CE mark	CE mark	Color rendering index (CRI)	>70
Warranty period	3 years	Light source color	740 neutral white
Flammability mark	For mounting on normally flammable surfaces	Optical cover type	Polycarbonate micro lens optic
Light Technical		Operating and Electrical	
Luminous Flux	13,300 lm	Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz

GreenVision Xceed Gen2

Power Consumption	95 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Gray
Overall length	446 mm
Overall width	310 mm
Overall height	138 mm
Effective projected area	0.14 m²
Dimensions (Height x Width x Depth)	138 x 310 x 446 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM < 5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	100,000 hour(s)
---------------------------	-----------------

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BRP381 LED133/NW 95W 220-240V DM PSR
Full product name	BRP381 LED133/NW 95W 220-240V DM PSR
Full product code	871951454603500
Order code	911401875798
Material Nr. (12NC)	911401875798
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514546035
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514546035

Dimensional drawing



