



Smartbright Waterproof G3 WT068C

WT068C CW LED36 L1200 PSU

Smartbright Waterproof G3 WT068C, 33 W, 3600 lm, 6500 K

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Product data

General Information		Power Factor (Fraction) 0.9	
Light source engine type	LED	Number of products on MCB of 16 A type B 1	
CE mark	CE mark		
Light Technical		Temperature	
Luminous Flux	3,600 lm	Ambient temperature range -20 to +45 °C	
Correlated Color Temperature (Nom)	6500 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	110 lm/W	Dimmable No	
Color rendering index (CRI)	>80	Control interface -	
Light source color	865 cool daylight	Mechanical and Housing	
Optical cover type	-	Housing Material Polycarbonate	
Operating and Electrical		Optical cover material Polycarbonate	
Input Voltage	220 to 240 V	Housing Color White and gray	
Line Frequency	50 or 60 Hz	Optical cover finish Opal	
Power Consumption	33 W	Overall length 1,188 mm	

Smartbright Waterproof G3 WT068C

Overall width	69 mm
Overall height	74 mm
Dimensions (Height x Width x Depth)	74 x 69 x 1188 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	WT068C CW LED36 L1200 PSU
Full product name	WT068C CW LED36 L1200 PSU
Full product code	871016336060799
Order code	911401881480
Material Nr. (12NC)	911401881480
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163360607
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163360720

Dimensional drawing

WT068C-4ft

