



# Coreline Slim Batten

## BN126C LED22S/840 PSU L600

Coreline Slim Batten, 17 W, 2200 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

### Product data

General Information		Temperature	
Light source engine type	LED	Ambient temperature range	-20 to +40 °C
CE mark	CE mark		
Light Technical		Controls and Dimming	
Luminous Flux	2,200 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	105 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	840 neutral white	Housing Material	Steel
Optical cover type	Polycarbonate Diffuser	Optical cover material	Polycarbonate
		Housing Color	White RAL 9003
		Optical cover finish	Opal
Operating and Electrical		Overall length	600 mm
Input Voltage	220 to 240 V	Overall width	65 mm
Line Frequency	50 or 60 Hz	Overall height	65 mm
Power Consumption	17 W	Dimensions (Height x Width x Depth)	65 x 65 x 600 mm
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	80	Approval and Application	
		Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
		Mech. impact protection code	IK04 [0.5 J standard plus]

Coreline Slim Batten

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BN126C LED22S/840 PSU L600
Full product name	BN126C LED22S/840 PSU L600
Full product code	692382863851199

Order code	911401898780
Material Nr. (12NC)	911401898780
Local order code	BN12622L8402FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638511
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638573

Dimensional drawing

