# **PHILIPS** Lighting



# **ClearFlood Large**

# BVP651 LED550-4S/740 OFA52 ALU PSU

ClearFlood large, LED module 55000 lm, LED, Power supply unit (On/Off), Optiflux asymmetrical axis angle 52°, Aluminum

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications. It also includes all the necessary control features and interfaces to make it future-proof and even more efficient. ClearFlood Large lets you choose the exact number of lumens you need for your application. Incorporating extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution offering an outstanding lux/euro ratio and energy savings of up to 40% (without the use of additional controls). The wide choice of optics ensures maximum application coverage. ClearFlood Large is easy to install – you simply plug it in and select the best option for your needs. Perfect for replacing conventional technology and enabling intelligent lighting control while retaining the same electrical installation and poles.

#### **Product data**

General Information	
Lamp family code	LED550 [LED module 55000 lm]
Light source replaceable	Yes
Number of gear units	2 units
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value. * At
	extreme ambient temperatures the luminaire

	might automatically dim down to protect
	components
Light source engine type	LED
Service tag	Yes
Product family code	BVP651 [ClearFlood large]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable
	surfaces
ENEC mark	ENEC mark

# ClearFlood Large

EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	48,000 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	142 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	39° - 11° x 98°
Optic type outdoor	Optiflux asymmetrical axis angle 52°

#### **Operating and Electrical**

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	1.32 ms
Power Consumption	335 W
Power Factor (Fraction)	0.98
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type	3
В	

## Temperature

Ambient temperature range

#### Controls and Dimming

•		
Dimmable	No	
Driver/power unit/transformer	Power supply unit (On/Off)	
Control interface	-	
Constant light output	No	

-40 to +50 °C

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	880 mm
Overall width	656 mm
Overall height	100 mm
Effective projected area	0.41 m <sup>2</sup>
Dimensions (Height x Width x Depth)	100 x 656 x 880 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV
	differential mode and 4 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Initial Performance (IEC Compliant	)
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Comp	liant)
Driver failure rate at 5000 h	0.005 %
Control gear failure rate at median useful	L 0.1 %
life 100000 h	
life 100000 h Lumen maintenance at median useful	L96
	L96
Lumen maintenance at median useful	L96
Lumen maintenance at median useful	L96
Lumen maintenance at median useful life* 100000 h	L96 25 °C
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq	
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data	25 °C
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name	25 °C BVP651 LED550-4S/740 OFA52 ALU PSU
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name Full product code	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU 871869910790100
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU 871869910790100 10790100
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name Full product code	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU 871869910790100
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name Full product code Order code	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU 871869910790100 10790100
Lumen maintenance at median useful life* 100000 h Application Conditions Performance ambient temperature Tq Product Data Order product name Full product name Full product code Order code Material Nr. (12NC)	25 °C 25 °C BVP651 LED550-4S/740 OFA52 ALU PSU BVP651 LED550-4S/740 OFA52 ALU PSU 871869910790100 10790100 912300023746

8718699107901

EAN/UPC - Case

# **ClearFlood Large**

### Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 25 - data subject to change