PHILIPS Lighting



Jargeau 400 LED

BPP641 LED43-4S/740 PSU II DS50 FG BK 76

JARGEAU 400 GEN2 LED, LED module 4300 lm, 740 neutral white, Safety class II, Distribution symmetrical 50, Flat glass, Black, Post-top for diameter 76 mm

Jargeau 400 LED combines the symbolic features of the first four-sided street lamps of the 19th century with the technical performance of 21st century luminaires. It incorporates the energy-efficient LEDGINE - O engine with high-performance optics, while at the same time retaining the character of the original four-sided fixture. Designed for installation at heights of 4-6 meters, this luminaire is well suited to urban landscapes and ideal for illuminating city centers, historical areas, old villages, streets, alleys, squares and parks. Jargeau 400 LED can also enable the benefits of the latest technologies developed by Philips Lighting, including the CityTouch connected lighting system.

Product data

General Information	
Lamp family code	LED43 [LED module 4300 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value. * At
	extreme ambient temperatures the luminaire

	might automatically dim down to protect
	components
Light source engine type	LED
Product family code	BPP641 [JARGEAU 400 GEN2 LED]
Lighting Technology	LED
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0.03

Jargeau 400 LED

Luminous Flux	3,440 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	127 lm/W
Color rendering index (CRI)	≥70
Number of light sources	20
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	152° x 155°
Optic type outdoor	Distribution symmetrical 50

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	27 W
Power Factor (Fraction)	0.97
Connection	Plug-in connector 2-pole Wieland/Adels
	compatible

Cable

Number of products on MCB of 16 A type 20

в

Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate

Glass

Black

Flat

Aluminum

Post-top for diameter 76 mm

Fixation diameter	Mounting device diameter 76 mm
Overall length	400 mm
Overall width	400 mm
Overall height	864 mm
Effective projected area	0.13 m²
Dimensions (Height x Width x Depth)	864 x 400 x 400 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	
Protection class IEC	Safety class II
Initial Performance (IEC Complian	t)
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Comp	pliant)
Control gear failure rate at median usefu life 100000 h	ul 10 %
Lumen maintenance at median useful life* 100000 h	95
Application Conditions	
Performance ambient temperature Tq	25 °C
Product Data	
Order product name	BPP641 LED43-4S/740 PSU II DS50 FG BK 76
Full product name	BPP641 LED43-4S/740 PSU II DS50 FG BK 76
Full product code	871869910894600
Order code	10894600
Material Nr. (12NC)	912300023780
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699108946
Numerator - Packs per outer box	1

8718699108946

Clear

Optical cover finish

Optical cover material

Fixation material

Mounting device


Optical cover shape

Housing Color

EAN/UPC - Case

Jargeau 400 LED

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 30 - data subject to change