



# Micenas LED

## BSP791 LED61-4S/830 DN10 FG BK

MICENAS, LED module 6100 lm, 830 warm white, Power supply unit (On/Off), Safety class I, Distribution narrow 10, Flat glass, Black

Combining contemporary aesthetics and classical inspiration, Micenas gen2 LED is an elegant presence in both modern and traditional urban settings. With its 2nd-generation LED module, Micenas gen2 LED ensures a higher light output over an extended service life and higher energy efficiency. The Eco-designed luminaire has retained its original avant-garde form and provides comfortable ambient lighting. The housing has a textured black finish that underlines the luminaire's timeless shape, which blends in harmoniously with walls and facades. And a number of dedicated brackets are available, ensuring the decorative integration of luminaire and pole.

### Product data

#### General Information

Lamp family code	LED61 [LED module 6100 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire

	might automatically dim down to protect components
Light source engine type	LED
Service tag	Yes
Product family code	BSP791 [MICENAS]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

# Micenas LED

Light Technical	
Upward light output ratio	0.03
Luminous Flux	5,270 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	112 lm/W
Color rendering index (CRI)	≥80
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	26° - 7° x 157°
Optic type outdoor	Distribution narrow 10

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	80 A
Inrush time	0.15 ms
Power Consumption	47 W
Power Factor (Fraction)	0.91
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	9

Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Black
Mounting device	Suspension set simple, standard

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	385 mm
Overall width	385 mm
Overall height	561 mm
Effective projected area	0.102 m²
Dimensions (Height x Width x Depth)	561 x 385 x 385 mm

Approval and Application	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.433, 0.403) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L96

Application Conditions	
Performance ambient temperature Tq	25 °C

Product Data	
Order product name	BSP791 LED61-4S/830 DN10 FG BK
Full product name	BSP791 LED61-4S/830 DN10 FG BK
Full product code	871869910898400
Order code	10898400
Material Nr. (12NC)	912300023784
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699108984
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699108984

## Micenas LED

### Dimensional drawing

