PHILIPS Lighting



FlowStar

BGB300 LED660-4S/740 PSD DSM11 D9 MDD

FLOWSTAR LARGE, 200, LED module 66000 lm, LED, 415 W, Power supply unit with DALI interface, Distribution symmetrical medium 11, Flat glass, 148° x 148°, DALI, Suspension set simple, standard

Tunnel operators are looking for an LED solution for both interior and entrance lighting that delivers cost, safety and availability benefits over the full lifetime of the product. FlowStar's stainless-steel modular build and dedicated LED design provide a long-lasting and efficient LED alternative to conventional HPS lighting. FlowStar can also be combined with our controls and services for the highest levels of performance.

Product data

General Information		Light sou
Lamp family code	LED660 [LED module 66000 lm]	Product f
Light source replaceable	No	Lighting 1
Number of gear units	3 units	CE mark
Driver included	Yes	Warranty
Remarks	*-Per Lighting Europe guidance paper	Flammab
	"Evaluating performance of LED based	
	luminaires - January 2018": statistically there	ENEC ma
	is no relevant difference in lumen	EU RoHS
	maintenance between B50 and for example	
	B10. Therefore, the median useful life (B50)	Light Te
	value also represents the B10 value. * At	Upward l
	extreme ambient temperatures the luminaire	Luminous
	might automatically dim down to protect	Standard
	components	Standard

Light source engine type	LED
Product family code	BGB300 [FLOWSTAR LARGE]
Lighting Technology	LED
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable
	surfaces
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	54,780 lm
Standard tilt angle posttop	O°
Standard tilt angle side entry	O°

FlowStar

4000 K
132 lm/W
>70
200
740 neutral white
Flat glass
148° x 148°
Distribution symmetrical medium 11

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	415 W
Power Factor (Fraction)	0.99
Connection	Mains outlet socket and 2 DALI sockets
Cable	-
Number of products on MCB of 16 A type	2
В	

Temperature

Ambient temperature range

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

-30 to +40 °C

Housing Material	Stainless steel
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Steel
Mounting device	Suspension set simple, standard
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	725 mm

Overall width	620 mm
Overall height	66.5 mm
	0.4495 m ²
Effective projected area	67 x 620 x 725 mm
Dimensions (Height x Width x Depth)	67 X 620 X 725 Milli
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.433. 0.403) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Comp	liant)
Control gear failure rate at median usefu	
life 100000 h	
Lumen maintenance at median useful	L95
life* 100000 h	
Application Conditions	
Performance ambient temperature Tq	25 ℃
Maximum dim level	10%
Product Data	
Order product name	BGB300 LED660-4S/740 PSD DSM11 D9
	MDD
Full product name	BGB300 LED660-4S/740 PSD DSM11 D9
-	MDD
Full product code	871869912035100
Order code	912300023896
Material Nr. (12NC)	912300023896
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699120351
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699120351

FlowStar

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change