



# UrbanStar

## BDS100 LED14/740 I DS50 DGR CLO-LS-8 50%

UrbanStar, LED module 1400 lm, 740 neutral white, Safety class I, Distribution symmetrical 50, Grey, Constant light output and LumiStep dimming 8 hours

In residential areas, the familiar conical luminaires equipped with PL-L or HPL lamps can now be replaced by a charming design luminaire incorporating leading-edge LED technology – without losing any of the visual balance and ambiance provided by the former solution. UrbanStar is a highly efficient LED luminaire, which enables a significant reduction in energy consumption compared to PL-L solutions. It has been specially designed for residential applications, and its translucent cone delivers very comfortable light.

### Product data

General Information	
Lamp family code	LED14 [LED module 1400 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components

Light source engine type	LED
Product family code	BDS100 [UrbanStar]
Lighting Technology	LED
Value ladder	Performance
Embedded control	Constant light output and LumiStep dimming 8 hours
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Light Technical	
Upwards light output ratio	0.03
Luminous Flux	1,188 lm

Standard tilt angle post-top	0°
Standard tilt angle side entry	-
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	131 lm/W
Colour rendering index (CRI)	≥70
Light source colour	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152° x 155°
Optic type outdoor	Distribution symmetrical 50

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	9.1 W
Average CLO power consumption	9.2 W
End CLO power consumption	9.2 W
Inrush current	15 A
Inrush time	0.295 ms
Power Consumption	9.1 W
Power Factor (Fraction)	0.97
Connection	Plug-in connector 2-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	29

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	Analogue
Constant light output	Yes

#### Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Glass
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Pole-mounting bracket diameter 76 mm
Optical cover/lens shape	Conical
Optical cover/lens finish	Frosted

Overall length	403 mm
Overall width	350 mm
Overall height	914 mm
Overall diameter	76 mm
Effective projected area	0.155 m²
Dimensions (height x width x depth)	914 x 350 x 403 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 6 kV common mode
Sustainability rating	-
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/-7%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L100

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	20%

#### Product Data

Order product name	BDS100 LED14/740 I DS50 DGR CLO-LS-8 50%
Full product name	BDS100 LED14/740 I DS50 DGR CLO-LS-8 50%
Full EOC	871869945042700
Order code	45042700
Material no. (12 NC)	912300023990
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699450427
Numerator – packs per outer box	1
EAN/UPC – Case	8718699450427

## Dimensional drawing

