# **PHILIPS** Lighting



## Luma

### BGP627 LED550-4S/740 PSU II DX10 GR CLO

LUMA 3, LED module 55000 lm, 740 neutral white, Power supply unit (On/Off), Safety class II, Distribution extra wide 10, Acrylate micro-lens optic, Grey, Philips standard surge protection level, Spigot for diameter 76 mm

Luma is a high-performance road-lighting luminaire with a clear design identity, offering a perfectly cooled, fit-and-forget solution for all streets and roads. The lumen package, lifetime and energy profile can be tuned to create the desired solution in terms of energy and cost savings. Luma can be programmed to keep the flux of the LEDs at a predefined constant level over the lifetime of the luminaire – by increasing the operating current over time to compensate for the LED lumen depreciation. Luma uses the high-performance LEDGINE-O engine with latest LED performance and a wide range of optics to latest standards. Moreover Luma's trully flat design prevents upward light to optimize the light distribution for varying road geometries and/or glare restrictions, the tilt angle can easily be adjusted on installation. Luma is also equipped with a dedicate light recipes that preserves a dark night sky.

#### Product data

General Information	
General mormation	
Lamp family code	LED550 [LED module 55000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen

	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value. * At
	extreme ambient temperatures the luminaire
	might automatically dim down to protect
	components
Light source engine type	LED
Product family code	BGP627 [LUMA 3]
Lighting Technology	LED

#### Luma

Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	47,040 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	≥70
Light source color	740 neutral white
Optical cover type	Acrylate micro-lens optic
Luminaire light beam spread	20° - 4° x 150°
Optic type outdoor	Distribution extra wide 10

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	325 W
Average CLO power consumption	340 W
End CLO power consumption	355 W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	335 W
Power Factor (Fraction)	0.98
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type	8

в

Temperature

Ambient temperature range

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	Analog
Constant light output	Yes
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate

-40 to +50 °C

Optic material

Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 76 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	999 mm
Overall width	435 mm
Overall height	235 mm
Overall diameter	76 mm
Effective projected area	0.079 m²
Dimensions (Height x Width x Depth)	235 x 435 x 999 mm

#### **Approval and Application**

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)		
Luminous flux tolerance	+/-7%	
Initial chromaticity	(0.382, 0.379) SDCM <5	
Power consumption tolerance	+/-10%	
Init. Color Rendering Index Tolerance	+/-2	
Over Time Performance (IEC Compliant)		
Control gear failure rate at median useful 10 %		
life 100000 h		

Lumen maintenance at median useful	L100
life* 100000 h	

#### **Application Conditions**

Performance ambient temperature Tq	25 ℃
Maximum dim level	Not applicable

#### Product Data

Order product name	BGP627 LED550-4S/740 PSU II DX10 GR CLO
Full product name	BGP627 LED550-4S/740 PSU II DX10 GR CLO
Full product code	871869945996300
Order code	912300024016
Material Nr. (12NC)	912300024016
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699459963
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699459963

Datasheet, 2023, September 4

#### Luma

#### Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change