



# Luma

## BGP621 LED55/740 II DN10 D11 GR 76

LUMA MINI, LED module 5500 lm, 740 neutral white, Power supply unit regulating, Safety class II, Distribution narrow 10, Acrylate micro-lens optic, Grey, Philips standard surge protection level, Spigot for diameter 76 mm

Luma is a REVOLED™ road-lighting luminaire with a clear design identity, offering a perfectly cooled, fit-and-forget solution for all streets and roads. The lumen package, lifetime and energy profile can be tuned to create the desired solution in terms of energy and cost savings. Luma can be programmed to keep the flux of the LEDs at a predefined constant level over the lifetime of the luminaire – by increasing the operating current over time to compensate for the LED lumen depreciation. This eliminates over-lighting at the beginning, enabling additional extra energy savings. Luma’s truly flat design prevents upward light, and the OPTIFLUX™ lens optics meet current lighting standards. To optimize the light distribution for varying road geometries and/or glare restrictions, the tilt angle can easily be adjusted on installation.

### Product data

General Information		
Lamp family code	LED55 [LED module 5500 lm]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires - January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example	B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type		LED
Product family code		BGP621 [LUMA MINI]
Lighting Technology		LED
CE mark		Yes
Warranty period		5 years

Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

#### Light Technical

Upward light output ratio	0
Luminous Flux	5,096 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color rendering index (CRI)	≥70
Light source color	740 neutral white
Optical cover type	Acrylate micro-lens optic
Luminaire light beam spread	11° - 58° x 156°
Optic type outdoor	Distribution narrow 10

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	0.15 ms
Power Consumption	33.3 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	9

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey

Mounting device	Spigot for diameter 76 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	649 mm
Overall width	310 mm
Overall height	235 mm
Overall diameter	76 mm
Effective projected area	0.055 m²
Dimensions (Height x Width x Depth)	235 x 310 x 649 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L95

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	25%

#### Product Data

Order product name	BGP621 LED55/740 II DN10 D11 GR 76
Full product name	BGP621 LED55/740 II DN10 D11 GR 76
Full product code	871869947916900
Order code	47916900
Material Nr. (12NC)	912300024079
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699479169
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699479169

## Dimensional drawing

