# **PHILIPS** Lighting



# **OptiVision LED gen2**

# BVP515 1290/740 380-400 BV AWB D9 T20 LO

OptiVision LED gen2, LED High Brightness, 740 neutral white, 380/400 V, Asymmetrical wide beam

The Philips OptiVision LED gen2 floodlighting system provides a complete lighting solution for the simplest through to the most complex area and recreational sports lighting applications. The high-efficiency floodlights come with three or two LED light modules, which function with an external driver box – separate for use at a distance from the floodlight (BV), or pre-fixed onto the mounting bracket of the floodlight (HGB) for ease of installation and lower initial cost. They meet the highest performance standards, provide outstanding light quality, and ensure safety and visual comfort. OptiVision LED gen2 offers new possibilities to reduce energy consumption and increase flexibility (instant start, programmable lighting levels) when used in conjunction with Philips' advanced system controls and sensors. The floodlights are also compatible with other external control systems via DALI protocol.

#### **Product data**

General Information	
Lamp family code	LED-HB [LED High Brightness]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value. * At

	extreme ambient temperatures the luminaire
	might automatically dim down to protect
	components
Light source engine type	LED
Product family code	BVP515 [OptiVision LED gen2]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark

## **OptiVision LED gen2**

EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	102,000 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	≥70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	18° - 7° x 119°
Optic type outdoor	Asymmetrical wide beam

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	750 mm
Overall width	616 mm
Overall height	600 mm
Effective projected area	0.34 m²
Dimensions (Height x Width x Depth)	600 x 616 x 750 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV
	differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)		
Luminous flux tolerance +/-7%		
Initial chromaticity	(0.367, 0.358) SDCM <5	
Power consumption tolerance	+/-10%	
Init. Color Rendering Index Tolerance +/-2		

Over Time Performance (IEC Compliant)		
Control gear failure rate at median	5 %	
useful life 50000 h		
Lumen maintenance at median useful	L80	
life* 50000 h		
Application Conditions		
Performance ambient temperature Tq	25 °C	
Maximum dim level	10%	

Product Data	
Order product name	BVP515 1290/740 380-400 BV AWB D9 T20
	LO
Full product name	BVP515 1290/740 380-400 BV AWB D9 T20
	LO
Full product code	871869948180300
Order code	912300024107
Material Nr. (12NC)	912300024107
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699481803
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699481803

Operating and Electrical		
Input Voltage	380/400 V	
Line Frequency	50 Hz	
Inrush current	30 A	
Inrush time	0.016 ms	
Power Consumption	981 W	
Power Factor (Fraction)	0.95	
Connection	Push-in connector and pull relief	
Cable	-	
Number of products on MCB of 16 A type -		
В		

_	en	npe	rati	ire	

Ambient temperature range

Dimmable	Yes	
Driver/power unit/transformer	Power supply unit with DALI interface	
	external	
Control interface	DALI	
Constant light output	No	

-40 to +50 °C

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable

## **OptiVision LED gen2**

#### Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change