



# TownTune Asymmetric DTC

## BDP267 LED24-4S/740 II DM33 CLO SRT SRB

TOWNTUNE ASYMMETRIC DTC, LED Module 2400 lm, LED, 740 neutral white, Power supply unit with DALI and SystemReady interface, 220 to 240 V, 50 or 60 Hz, Safety class II, Distribution medium 33, Polycarbonate bowl/cover UV-resistant, Gray, Philips standard surge protection level, Universal for diameter 48 to 60 mm adjustable

Designed to enhance existing and scalable urban spaces, the Philips TownTune family offers all the latest lighting innovations in terms of performance, quality of light and connectivity. The family consists of four solutions: a Central Post Top (CPT), an Asymmetric Spigot Post Top / Side Entry version (ASY), a version with an extending Lyre post top bracket (Lyre), and a Central Post Top with a Conical Comfort Bowl (CCB). Each TownTune luminaire can be customized with a choice of different shapes on top of the housing, plus there's the option to add a decorative ring, which comes in two colors (excluding CCB). Design options that enable you to create your very own lighting signature and bring a distinctive identity to districts and cities. In addition, every luminaire in the TownTune family is uniquely identifiable, thanks to the Signify Service tag app. By simply scanning a QR code, placed inside the door of the mast or directly on the luminaire, you can instantly access the configuration of the luminaire. This makes maintenance and programming operations faster and easier and enables you to create your digital library of lighting assets and spare parts. TownTune also uses the Philips LEDGINE-O lighting platform, ensuring you always have the right amount and direction of light on your street. Furthermore, thanks to being system ready (SR), TownTune is also future proof. A solution that's ready to be paired with both standalone and advanced control and lighting software applications such as Interact City.



TownTune Asymmetric DTC

Product data

General Information	
Lamp family code	LED24 [LED Module 2400 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Service tag	Yes
Product family code	BDP267 [TOWNTUNE ASYMMETRIC DTC]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	1,932 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	122 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	4° - 58° × 149°
Optic type outdoor	Distribution medium 33
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	15.8 W
Average CLO power consumption	15.8 W
End CLO power consumption	16 W
Inrush current	18 A
Inrush time	0.32 ms
Power Consumption	15.8 W
Power Factor (Fraction)	0.98
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B	23
Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI and SystemReady interface
Control interface	DALI
Constant light output	Yes
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Universal for diameter 48 to 60 mm adjustable
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall height	248 mm
Overall diameter	477 mm
Effective projected area	0.052 m²
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Philips standard surge protection level
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance at median useful life* 100000 h	L100
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	10%



# TownTune Asymmetric DTC

Product Data	
Order product name	BDP267 LED24-4S/740 II DM33 CLO SRT SRB
Full product name	BDP267 LED24-4S/740 II DM33 CLO SRT SRB
Full product code	871869949763700
Order code	49763700

Material Nr. (12NC)	912300024204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699497637
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699497637

## Dimensional drawing

