



CitySoul gen2 LED Mini

BPP530 LED60-4S/830 II DM D9 SRT CTG-

CitySoul gen2 Mini, LED module 6000 lm, 830 warm white, Power supply unit with DALI and SystemReady interface, Safety class II, Distribution medium 50, Clear glass, Grey, Philips standard surge protection level, Post-top for diameter 60 mm

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

Product data

General Information		Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Lamp family code	LED60 [LED module 6000 lm]	Light source engine type	LED
Light source replaceable	Yes	Product family code	BPP530 [CitySoul gen2 Mini]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Value ladder	Performance

CitySoul gen2 LED Mini

CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.03
Luminous Flux	5,100 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color rendering index (CRI)	≥80
Number of light sources	30
Light source color	830 warm white
Optical cover type	Clear glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 50

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46 W
Power Factor (Fraction)	0.96
Connection	Screw connection block
Cable	-
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Wireless Dim
Driver/power unit/transformer	Power supply unit with DALI and SystemReady interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover material	Glass

Fixation material	Aluminum
Housing Color	Grey
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	165 mm
Overall diameter	630 mm
Effective projected area	0.05 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L92

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BPP530 LED60-4S/830 II DM D9 SRT CTG-
Full product name	BPP530 LED60-4S/830 II DM D9 SRT CTG-
Full product code	871869987867200
Order code	87867200
Material Nr. (12NC)	912300024410
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699878672
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699878672

CitySoul gen2 LED Mini

Dimensional drawing

