



CitySoul gen2 LED Mini

BRP530 LED60-4S/830 II DM50 D9 SRG10ALGR

CitySoul gen2 Mini, LED module 6000 lm, 830 warm white, Power supply unit with DALI interface, Safety class II, Distribution medium 50, Flat glass, Grey, Luminaire surge protection level up to 10 kV differential mode and 10 kV common mode, Side-entry for diameter 60 mm

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

Product data

General Information		Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Lamp family code	LED60 [LED module 6000 lm]		
Light source replaceable	Yes		
Number of gear units	Unit	Light source engine type	LED
Driver included	Yes	Product family code	BRP530 [CitySoul gen2 Mini]
		Lighting Technology	LED

CitySoul gen2 LED Mini

Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upwards light output ratio	0.03
Luminous Flux	5,100 lm
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	110 lm/W
Colour rendering index (CRI)	≥80
Light source colour	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 50

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46.5 W
Power Factor (Fraction)	0.98
Connection	Screw connection block
Cable	-
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Side-entry for diameter 60 mm

Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall height	95 mm
Overall diameter	645 mm
Effective projected area	0.052 m²
Parts colour	All parts coloured

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 10 kV differential mode and 10 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L97

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BRP530 LED60-4S/830 II DM50 D9 SRG10ALGR
Full product name	BRP530 LED60-4S/830 II DM50 D9 SRG10ALGR
Full EOC	871869989204300
Order code	89204300
Material no. (12 NC)	912300024531
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699892043
Numerator – packs per outer box	1
EAN/UPC – Case	8718699892043

CitySoul gen2 LED Mini

Dimensional drawing

