



iColor Accent Compact, RGBW

iColor Accent Compact, RGBW, 1228.5 mm (48.4 in), Translucent Lens

iColor Accent Compact, RGBW, 1228.5 mm (48.4 in), Translucent Lens

iColor Accent Compact, RGBW is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact, RGBW adds a separate white LED, creating better-quality whites compared to RGB. iColor Accent Compact, RGBW accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact, RGBW: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data

General information	
Light source colour	RGBW
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Light technical	
On-axis intensity in candela	57
Mechanical and housing	
Length	1220 mm


Colour	Aluminum
Approval and application	
Energy Efficiency Class	G
Vibration standard	Complies with ANSI C136.31, 3G
FCC mark	FCC Class A
Vibration rating	Complies with ANSI C136.31, 3G
	942289
Initial performance (IEC compliant)	
Initial LED luminaire efficacy at RGB operation	34.8 lm/W

iColor Accent Compact, RGBW


Initial input power	28.5 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Reported	50000
Lumen Maintenance 80% at 50 °C Reported	50000
Product data	
Full product code	871869921873799

Order product name	BCS425 RGBW FR ETH L1220 PP19
EAN/UPC – product	8718699218737
Order code	101-000200-09
SAP numerator – quantity per pack	1
Numerator – packs per outer box	9
SAP material	912400136258
Net Weight (Piece)	1.640 kg
Commercial Code	101-000200-09
Catalogue number description	iColor Accent Compact, RGBW, 1228.5 mm (48.4 in), Translucent Lens

Dimensional drawing



BCS425 RGBW FR ETH L1220 PP19



BCS425 RGBW FR ETH L1220 PP19

