



PureStyle Compact Powercore RGB

PureStyle Compact Powercore, RGB, 100° x 100° (Native beam), Low Power, 305 mm (12 in)

PureStyle Compact Powercore, RGB, 100° x 100° (Native beam), Low Power, 305 mm (12 in)

Innovative PureStyle Compact Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle Compact delivers exceptionally high-quality light for a wide range of interior applications from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data

General information	
Light source colour	RGBA
Optical cover/lens type	PC [Polycarbonate bowl/cover]
CE mark	CE mark
UL mark	UL and cUL mark
Operating and electrical	
Input Voltage	100 to 277 V
Mechanical and housing	
Housing material	Aluminum extruded
Length	305 mm
Colour	White


Approval and application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Class	G
FCC mark	FCC Class B
	915361
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	212 lm
Initial LED luminaire efficacy	24.1 lm/W
Initial LED luminaire efficacy at RGB	24.1 lm/W
operation	
Initial input power	4 W

PureStyle Compact Powercore RGBA

Application conditions	
Ambient temperature range	-20 to +50 °C
Product data	
Full product code	871951408403299
Order product name	SA501X RGBA LO L305
EAN/UPC – product	8719514084032
Order code	123-000028-02
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25

SAP material	912400137114
Net Weight (Piece)	0.240 kg
Commercial Code	123-000028-02
Catalogue number description	PureStyle Compact Powercore, RGBA, 100° x 100° (Native beam), Low Power, 305 mm (12 in)

Dimensional drawing



SA501X RGBA LO L305

