



CoreLine Recessed Spot

RS141B LED9-32-/830 PSR PI6 WH

CoreLine Recessed Spot, 11 W, 900 lm, 3000 K, Analog, Beam angle 32°, White RAL9010

CoreLine Recessed Spot delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. CoreLine Recessed Spot is a recessed spot range designed to replace halogen-based luminaires. Its halogen-like look and attractive price make it easier for customers to make the switch to LED. This product provides a natural lighting effect for accent lighting applications, as well as instant energy savings and much longer lifetime – an environmentally friendly solution. With the push-in connectors, installation is fast and straightforward.

Product data

General Information		Flammability mark	
Light source replaceable	No		For mounting on normally flammable surfaces
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	ENEC mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Warranty period	5 years
		EU RoHS compliant	Yes
		Value ladder	Performance
Lighting Technology		Light Technical	
Glow-wire test	Temperature 650 °C, duration 30 s	Luminous Flux	900 lm
		Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	82 lm/W
		Color rendering index (CRI)	85
		Beam angle of light source	32 degree(s)

CoreLine Recessed Spot

Light source color	830 warm white
Optic type	Beam angle 32°
Luminaire light beam spread	32°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	7 A
Inrush time	500 ms
Power Consumption	11 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	40

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White RAL9010
Optical cover finish	Clear
Overall height	59.5 mm
Overall diameter	95 mm

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70

Application Conditions


Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	RS141B LED9-32-/830 PSR PI6 WH
Full product name	RS141B LED9-32-/830 PSR PI6 WH
Full product code	871869938283499
Order code	912401483037
Material Nr. (12NC)	912401483037
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699382834
Numerator - Packs per outer box	18
EAN/UPC - Case	8718699383107



Dimensional drawing



CoreLine Recessed Spot

