



# FastSet, Surface Mounted

## SM150C LED60S/840 PSU TW3 PI5 L1440

840 neutral white, Power supply unit (On/Off), Connection unit 5-pole

Upgrading to LED is a key trend in office applications. Recognizing the need for an easy to use luminaire that can work as the perfect 1:1 replacement of conventional office lighting, we developed FastSet. This luminaire is an ideal choice to quickly achieve the benefits of LED lighting since being the perfect 1:1 replacement, no additional lighting calculation is needed prior to the LED lighting installation. The luminaire simply fits into all different indoor applications. Moreover, it is available in both standalone and through-wiring versions, which makes the luminaires ready-to-connect at a later stage.

### Product data

General Information			
Light source replaceable	No	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	-
Lighting Technology	LED	Glow-wire test	Temperature 850 °C, duration 30 s
Value ladder	Performance	EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	6,000 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	109 lm/W
		Color rendering index (CRI)	≥80

FastSet, Surface Mounted

Beam angle of light source	116 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	100°
Unified glare rating CEN	25

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	8 A
Inrush time	0.06 ms
Power Consumption	55 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,440 mm
Overall width	160 mm
Overall height	61 mm

Dimensions (Height x Width x Depth)	61 x 160 x 1440 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.3828, 0.3803) 5SDCM
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Order product name	SM150C LED60S/840 PSU TW3 PI5 L1440
Full product name	SM150C LED60S/840 PSU TW3 PI5 L1440
Full product code	871869938127199
Order code	912401483059
Material Nr. (12NC)	912401483059
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699381271
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699381332

Dimensional drawing



## FastSet, Surface Mounted

