



# CoreLine Wall-mounted

## WL131V LED34S/840 PSR MDU WH

CoreLine Wall-mounted, 38 W, D480 mm, 3400 lm, 4000 K, Sensor-based dim, IP65

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information			
Lamp family code	LED34S [LED module, system flux 3400 lm]	Embedded control	Movement detection unit
Light source replaceable	No	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Service tag	Yes	Glow-wire test	Temperature 650 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Performance	Light Technical	
		Luminous Flux	3,400 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	90 lm/W
		Color rendering index (CRI)	80
		Beam angle of light source	120 degree(s)
		Light source color	840 neutral white

## CoreLine Wall-mounted

Optic type	Opal prismatic reflector
Optical cover type	Opal bowl with painted cover
Luminaire light beam spread	120°

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	NA W
Average CLO power consumption	NA W
End CLO power consumption	NA W
Inrush current	27 A
Inrush time	265 ms
Power Consumption	38 W
Power Factor (Fraction)	0.8
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB of 16 A type B	18

### Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Sensor-based dim
Constant light output	No

### Mechanical and Housing

Housing Material	Polyamide
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Overall length	480 mm
Overall width	480 mm

Overall height	95 mm
Overall diameter	480 mm
Dimensions (Height x Width x Depth)	95 x 480 x 480 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.39, 0.39) SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.7 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70


### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	WL131V LED34S/840 PSR MDU WH
Full product name	WL131V LED34S/840 PSR MDU WH
Full product code	871869938791499
Order code	912401483195
Material Nr. (12NC)	912401483195
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699387914
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699388096

## Dimensional drawing



## CoreLine Wall-mounted

