



Gear for SDW-T lamps

CSLS 100 SDW-T 220-240V 50/60Hz

CSLS electronic control unit with impregnated (HID "BASIC") or encapsulated (HID "Heavy Duty") electromagnetic ballasts

Product data

General Information	
Lamp type	SDW-T
Number of lamps	1 piece/unit
Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Response voltage	210 V
Mains voltage performance (AC)	-4%~+9%
Mains voltage safety (AC)	-10%~+10%
Output peak voltage (max.)	4500 V
Power losses (nom.)	4.0 W
Wiring	
Cable length from device to lamp	0.50 m
Wire strip length	6.0 mm
Ballast contact wire cross section	0.50-2.50 mm ²
Cable capacity output wires to earth (nom.)	50 pF
Connector type	Screw
System characteristics	
Rated ballast-lamp power	100 W

Temperature	
T ambient (max.)	65 °C
T storage (max.)	80 °C
T storage (min.)	-25 °C
T case lifetime (nom.)	90 °C
T-Case maximum (max.)	90 °C


Approval and Application	
Vibration standard	IEC68-2-6 F c
Approval marks	CE marking VDE-EMV certificate CB Certificate

Product Data	
Full product code	871150090870430
Order product name	CSLS 100 SDW-T 220-240V 50/60Hz
EAN/UPC – product	8711500908704
Order code	913619189966
Numerator – quantity per pack	1
Numerator – packs per outer box	18
Material no. (12NC)	913619189966
Net weight (piece)	0.259 kg

Warnings and Safety

Gear for SDW-T lamps

Dimensional drawing



Product

CSLS 100 SDW-T 220-240V 50/60Hz

CSLS 100 SDW-T 220-240V 50/60Hz

