



# HF-Regulator II for TL5 lamps

## HF-R 280 TL5/PL-L EII 220-240V 50/60Hz

Flat, lightweight high-frequency electronic regulating ballast, using 1-10V protocol for TL5 fluorescent lamps

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.5 mA
Inrush Current Width	0.15 ms
Inrush Current Peak (Max)	40 A
Number of Products on MCB (16A Type B) (Nom)	9
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
Ambient temperature range	-20 °C to 50 °C


Controls and Dimming	
Control Interface	1-10V
Mechanical and Housing	
Housing	L 425x30x21
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A1 BAT
Safety Standard	IEC 61347-2-3
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate VDE-EMV certificate

Product Data	
Order product name	HF-R 280 TL5/PL-L EII 220-240V 50/60Hz
Full product name	HF-R 280 TL5/PL-L EII 220-240V 50/60Hz
Full product code	871150091065330
Order code	91065330
Material Nr. (12NC)	913700609166
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500910653

# HF-Regulator II for TL5 lamps

Numerator - Packs per outer box	12
EAN/UPC - Case	8711500910660

## Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-R 280 TL5/PL-L EII 220-240V 50/60Hz	4.2 mm	22 mm	425 mm	415 mm	30 mm

