



# HF-Performer II Xtreme for TL5/TL-D lamps

## HF-P XT 258 TL-D EII 220-240V 50/60HZ

HF-Performer Xtreme is a unique X-technology from Philips that guarantees the highest lifetime reliability for lamps and enables an extra-long and reliable HF system life with an energy efficiency index (CELMA EEI) of A2.

### Product data

| Operating and Electrical                       |   |
|--|---|
| Input Voltage                                  | 220 to 240 V  |
| Line Frequency                                 | 50 to 60 Hz   |
| Input frequency                                | 50 to 60 Hz   |
| Inrush current width                           | 0.350 ms  |
| Inrush current peak (max.)                     | 31 A  |
| Number of products on MCB (16 A type B) (nom.) | 12  |
| Wiring   |   |
| Connector type input terminals                 | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Connector type output terminals                | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Temperature                                    |   |
| Ambient temperature range                      | -25 °C to 60 °C   |


| T-case lifetime (nom.)   | 75 °C   |
|--------------------------|---|
| T-Case maximum (max.)    | 75 °C   |
| Mechanical and Housing   |   |
| Housing                  | L 360x30x28                                     |
| Approval and Application |   |
| Ingress protection code  | IP20 [Finger-protected]                         |
| Energy efficiency index  | A2  |
| Safety standard          | IEC 61347-2-3                                   |
| Environmental standard   | ISO 14001                                       |
| Approval marks           | CE marking ENEC certificate VDE-EMV certificate |
| Product Data             |   |
| Order product name       | HF-P Xt 258 TL-D EII 220-240V 50/60Hz           |
| Full product name        | HF-P XT 258 TL-D EII 220-240V 50/60HZ           |
| Full EOC                 | 871150091206030                                 |
| Order code               | 91206030  |

# HF-Performer II Xtreme for TL5/TL-D lamps

|                                   |                |
|-----------------------------------|----------------|
| Material no. (12 NC)              | 913700618066   |
| Local order code                  | HFPXT258TLDEII |
| SAP numerator – quantity per pack | 1              |
| EAN/UPC – Product/Case            | 8711500912060  |

|                                 |               |
|---------------------------------|---------------|
| Numerator – packs per outer box | 12            |
| EAN/UPC – Case                  | 8711500912077 |

## Dimensional drawing



| Product                                  | D1     | C1      | A1       | A2       | B1      |
|--|--------|---------|----------|----------|---------|
| HF-P Xt 258 TL-D EII 220-240V<br>50/60Hz | 4.2 mm | 28.0 mm | 360.0 mm | 350.0 mm | 30.0 mm |

