



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 1 14/21/24/39 TL5 220-240V

HF-Performer Intelligent is a slim and lightweight high-frequency electronic ballast which makes it possible to exchange TL5 HE and HO lamps of the same length in order to maximize logistical flexibility in luminaire design and handling. With its smart power functionality based on Philips EII technology, HF-Performer Intelligent is optimized for maximum system efficiency (CELMA EEI A2 BAT) in combination with the TL5 and TL5 Eco lamp.

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Earth leakage current (max.)	0.5 mA
Inrush current width	0.35 ms
Inrush current peak (max.)	20 A
Number of products on MCB (16 A type B) (nom.)	18
Wiring	
Connector type input terminals	Insert
Connector type output terminals	Insert
Temperature	
Ambient temperature range	-25°C to 50°C


T-case lifetime (nom.)	75 °C
T-Case maximum (max.)	75 °C
Mechanical and Housing	
Housing	L360x30x22
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy efficiency index	A2 BAT
Safety standard	IEC 61347-2-3
Environmental standard	ISO 14001
Approval marks	CE marking ENEC certificate VDE-EMV certificate
Product Data	
Order product name	HF-Pi 1 14/21/24/39 TL5 EII 220-240V

HF-Performer Intelligent for TL5 HE/HO lamps

Full product name	HF-Pi 1 14/21/24/39 TL5 220-240V
Full EOC	871150091494130
Order code	91494130
Material no. (12 NC)	913700624066
SAP numerator – quantity per pack	1

EAN/UPC – Product/Case	8711500914941
Numerator – packs per outer box	12
EAN/UPC – Case	8711500914958

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 1 14/21/24/39 TL5 EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

