



# HF-Performer Intelligent for TL5 HE/HO lamps

## HF-Pi 2 14/21/24/39 TL5 220-240V

HF-Performer Intelligent for Master and ECO TL5 HE/HO, TL-D and PL-L lamps. HF-Performer Intelligent features automatic recognition of the connected lamp and is independently able to adjust its operation parameters exactly to the respective lamp. This results in a substantial benefit, especially for T5 lamps, as it means TL5 HE and HO lamps of the same length can be interchanged. With a choice of seven ballasts, the customer is able to handle efficiently every possible combination of Master TL5 and Eco, TL-D, and PL-L lamps.

### Product data


Operating and Electrical		Temperature	
Input Voltage	220 to 240 V	Ambient temperature range	-25 °C to 50 °C
Line Frequency	50 to 60 Hz	T-Case Lifetime (Nom)	75 °C
Input Frequency	50 to 60 Hz	T-Case Maximum (Max)	75 °C
Earth Leakage Current (Max)	0.5 mA	Mechanical and Housing	
Inrush Current Width	0.35 ms	Housing	L360x30x22
Inrush Current Peak (Max)	31 A	Approval and Application	
Number of Products on MCB (16A Type B) (Nom)	12	Ingress protection code	IP20 [Finger-protected]
Wiring		Energy Efficiency Index	A2 BAT
Connector Type Input Terminals	Insert	Safety Standard	IEC 61347-2-3
Connector Type Output Terminals	Insert	Environmental Standard	ISO 14001

## HF-Performer Intelligent for TL5 HE/HO lamps

<b>Approval Marks</b>	CE marking ENEC certificate VDE-EMV certificate
<b>Product Data</b>	
<b>Order product name</b>	HF-Pi 2 14/21/24/39 TL5 EII 220-240V
<b>Full product name</b>	HF-Pi 2 14/21/24/39 TL5 220-240V
<b>Full product code</b>	871150091500930
<b>Order code</b>	91500930

<b>Material Nr. (12NC)</b>	913700624266
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8711500915009
<b>Numerator - Packs per outer box</b>	12
<b>EAN/UPC - Case</b>	8711500915016

### Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 2 14/21/24/39 TL5 EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

