



HF-Performer Intelligent for TL5 HE/HO lamps

HF-Pi 2 14/21/24/39 TL5 220-240V

HF-Performer Intelligent is a slim and lightweight high-frequency electronic ballast which makes it possible to exchange TL5 HE and HO lamps of the same length in order to maximize logistical flexibility in luminaire design and handling. With its smart power functionality based on Philips EII technology, HF-Performer Intelligent is optimized for maximum system efficiency (CELMA EEI A2 BAT) in combination with the TL5 and TL5 Eco lamp.

Product data


Operating and Electrical		T-case lifetime (nom.)		T-Case maximum (max.)	
Input Voltage	220 to 240 V		75 °C		75 °C
Line Frequency	50 to 60 Hz	Mechanical and Housing			
Input frequency	50 to 60 Hz	Housing	L360x30x22		
Earth leakage current (max.)	0.5 mA	Approval and Application			
Inrush current width	0.35 ms	Ingress protection code	IP20 [Finger-protected]		
Inrush current peak (max.)	31 A	Energy efficiency index	A2 BAT		
Number of products on MCB (16 A type B) (nom.)	12	Safety standard	IEC 61347-2-3		
Wiring		Environmental standard	ISO 14001		
Connector type input terminals	Insert	Approval marks	CE marking ENEC certificate VDE-EMV certificate		
Connector type output terminals	Insert	Product Data			
Temperature		Order product name	HF-Pi 2 14/21/24/39 TL5 EII 220-240V		
Ambient temperature range	-25°C to 50°C				

HF-Performer Intelligent for TL5 HE/HO lamps

Full product name	HF-Pi 2 14/21/24/39 TL5 220-240V
Full EOC	871150091500930
Order code	91500930
Material no. (12 NC)	913700624266
Local order code	HFPI214212439
SAP numerator – quantity per pack	1

EAN/UPC – Product/Case	8711500915009
Numerator – packs per outer box	12
EAN/UPC – Case	8711500915016

Dimensional drawing



Product	D1	C1	A1	A2	B1
HF-Pi 2 14/21/24/39 TL5 EII 220-240V	4.2 mm	22 mm	360 mm	350 mm	30 mm

