



PrimaVision for CDM Elite MW

HID-PV 315 /S CDM 220-240V 50/60Hz

Highly reliable electronic drivers for medium-wattage lamps (210–400 W); designed to save energy via integrated one-step dimming and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.5 mA
Input Current (Nom)	1.53 A
Number of Products on MCB (16A Type B) (Nom)	4
Wiring	
Connector Type	Insert
Temperature	
Ambient temperature range	-20 °C to 55 °C
Mechanical and Housing	
Housing	/S

Approval and Application	
Safety Standard	EN60928, 60926
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate CB Certificate
Product Data	
Order product name	HID-PV 315 /S CDM 220-240V 50/60Hz
Full product name	HID-PV 315 /S CDM 220-240V 50/60Hz
Full product code	872790084311800
Order code	913700639466
Material Nr. (12NC)	913700639466
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500880888
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900843118

PrimaVision for CDM Elite MW

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 315 /S CDM 220-240V 50/60Hz	4.2 mm	60.0 mm	215.0 mm	204.5 mm	128.5 mm	111.5 mm

