



# PrimaVision for SDW-TG

## HID-PV 100 /S SDW-TG 220-240V 50/60Hz


Robust, lightweight and one-piece HID electronic gear for SDW-TG lamps (mini White SON) Lightweight, one-piece electronic gear for 50 and 100 W SDW-TG lamps (mini White SON)

### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Inrush current width	0.50 ms
Inrush current peak (max.)	33 A
Number of products on MCB (16 A type B) (nom.)	14
Wiring	
Cable length from device to lamp	2 m
Connector type	Insert
Temperature	
Ambient temperature range	-20°C to 60°C
T-case lifetime (nom.)	75 °C
T-Case maximum (max.)	85 °C
Mechanical and Housing	
Housing	/S

Approval and Application	
Approval marks	CE marking ENEC certificate CB certificate
Product Data	
Order product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
Full product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
Full EOC	872790088754900
Order code	88754900
Material no. (12 NC)	913700656566
Local order code	PV100SSDWTG
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500881861
Numerator – packs per outer box	10
EAN/UPC - Case	8727900887549

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 100 /S SDW-TG 220-240V 50/60Hz	4.5 mm	37.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

