



# PrimaVision Xtreme for CPO

## HID-PV Xt 140 CPO Q 208-277V

Highly reliable electronic drivers for CPO lamps; designed to save energy by offering better light efficiency than magnetic drivers and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection


### Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	208-240-277 V	Housing	Q
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Approval and Application	
Earth Leakage Current (Max)	0.7 mA	Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL
Inrush Current Width	0.47 ms	Safety Standard	IEC 607, 609, 926, 928 [No Standard for HID Lamp drivers exists. Requirements in these standards to be used if considered relevant for the product.]
Input Current (Nom)	0.75 A	Environmental Standard	ISO 14001
Inrush Current Peak (Max)	52 A	Approval Marks	F-Marking CE marking ENEC certificate VDE-EMV certificate
Number of Products on MCB (16A Type B) (Nom)	5	Product Data	
Wiring		Order product name	HID-PV Xt 140 CPO Q 208-277V
Cable Length From Device to Lamp	10 m	Full product name	HID-PV Xt 140 CPO Q 208-277V
Connector Type	WAGO series 804	Full product code	871829124147800
Temperature		Order code	913700685666
Ambient temperature range	-30 °C to 55 °C	Material Nr. (12NC)	913700685666
T-Case Lifetime (Nom)	80 °C	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718291241478
		Numerator - Packs per outer box	12

PrimaVision Xtreme for CPO

EAN/UPC - Case	8718291241485
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV Xt 140 CPO Q 208-277V	4.5 mm	40.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

