



# PrimaVision Mini for CDM

## HID-PV m 35 /S CDM 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design


#### **Product data**

Operating and Electrical		
Input Voltage	220 to 240 V	
Line Frequency	50 to 60 Hz	
Input Frequency	50 to 60 Hz	
Earth Leakage Current (Max)	0.5 mA	
Inrush Current Width	0.25 ms	
Inrush Current Peak (Max)	25 A	
Number of Products on MCB (16A Type B)	24	
(Nom)		
Wiring		
Cable Length From Device to Lamp	0.5 m	
Connector Type	Insert	
Temperature		
Ambient temperature range	-20 °C to 50 °C	
T-Case Lifetime (Nom)	85 °C	
T-Case Maximum (Max)	85 ℃	

Mechanical and Housing			
Housing	/S		
Approval and Application			
Approval Marks	CE marking ENEC certificate VDE certificate		
Product Data			
Order product name	HID-PV m 35 /S CDM 220-240V 50/60Hz		
Full product name	HID-PV m 35 /S CDM 220-240V 50/60Hz		
Full product code	871829167161900		
Order code	913700696166		
Material Nr. (12NC)	913700696166		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718291671619		
Numerator - Packs per outer box	12		
EAN/UPC - Case	8718291671626		

### **PrimaVision Mini for CDM**

#### Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m 35 /S CDM 220-240V	4.2 mm	30.2 mm	97.3 mm	88.3 mm	43.3 mm
50/60Hz					



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, February 27 - data subject to change