



Gear for SDW-T lamps

BSL 100 K202-A2-TS 230V 50Hz

CSLS electronic control unit with impregnated (HID 'BASIC') or encapsulated (HID 'Heavy Duty') electromagnetic ballasts

Avisos e Segurança


- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)

Dados do produto

Funcionamento e características elétricas		Nome do produto completo	
Tensão de entrada	230 V	Nome do produto completo	BSL 100 K202-A2-TS 230V 50Hz
Frequência de linha	50 Hz	Código do produto completo	871869674076700
Frequência de entrada	50 Hz	Código de encomenda	74076700
Cablagem		N.º material (12NC)	913700751826
Tipo de conector	Parafuso	Numerador – Quantidade por embalagem	1
Aprovação e aplicação		EAN/UPC - Produto/caixa	8718696740767
Marcas de aprovação	Marca CE Certificação ENEC	Numerador – Embalagens por caixa exterior	6
		EAN/UPC - Caso	8718696740774
Dados do produto			
Nome de produto da encomenda	BSL 100 K202-A2-TS 230V 50Hz		

Gear for SDW-T lamps

Desenho dimensional



Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6,2 mm

