




Sistem de control HID-CSLS pentru SDW

BSL 100 K202-A2-TS 230V 50Hz

Unitate de control electronică CSLS cu balasturi electromagnetice impregnate (HID "BASIC") sau încapsulate (HID "Heavy Duty")

Warnings and safety

- Climatic suitability CSLS and HID BASIC: restricted to built in situations under normal conditions
- Climatic suitability CSLS and HID Heavy Duty: use in luminaires under humid conditions (not drip-proof)



Catalog de date

Funcționare și sistem electric	
Tensiune de intrare	230 V
Frecvență linie	50 Hz
Frecvență de intrare	50 Hz
Cablaj	
Tip conector	Șurub
Aprobare și aplicație	
Mărci de omologare	Marcaj CE Certificat ENEC
Date despre produs	
Nume comandă produs	BSL 100 K202-A2-TS 230V 50Hz

Numele complet al produsului	BSL 100 K202-A2-TS 230V 50Hz
Full EOC	871869674076700
Cod de comandă	74076700
Număr material (12NC)	913700751826
Numărător SAP – Cantitate per pachet	1
EAN/UPC – Produs/Cutie	8718696740767
Numărător SAP – Pachete per exterior	6
EAN/UPC – Cutie	8718696740774

Sistem de control HID-CSLS pentru SDW

Cote



Product	A1	A2	B1	C1	D1
BSL 100 K202-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6,2 mm

