



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 50 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input frequency	50 Hz
Wiring	
Connector type	Screw
Approval and Application	
Approval marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 50 L33-A2-TS 230V 50Hz

Full product name	BSN 50 L33-A2-TS 230V 50Hz
Full EOC	871869674080400
Order code	74080400
Material no. (12 NC)	913700752026
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696740804
Numerator – packs per outer box	6
EAN/UPC - Case	8718696740811

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 50 L33-A2-TS 230V 50Hz	118 mm	103 mm	65 mm	53 mm	6.2 mm

