


Micropower Electronic ballast for TL/PL-S/-T/-C lamps (India)

EBS 114 230 SH

Compact, lightweight, high-frequency electronic ballast designed for TL (6-18 W) and compact fluorescent PL (7-24 W) lamps

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]

Temperature	
Ambient temperature range	0 °C to 40 °C
T-Case Maximum (Max)	75 °C

Product Data	
Order product name	EBS 114 230 SH
Full product name	EBS 114 230 SH
Full product code	871150088496100
Order code	913702243012
Material Nr. (12NC)	913702243012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884961
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900067989

Micropower Electronic ballast for TL/PL-S/-T/-C lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
EBS 114 230 SH	4.0 mm	22.0 mm	80.0 mm	65.0 mm	40.0 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.