

# HID-Basic BHL for HPL/HPI (India)

## BHL 400 X261

Impregnated electromagnetic ballasts of copper and steel construction for High-Pressure Mercury Vapor (HPL) lamps


### Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking

Product Data	
Order product name	BHL 400 X261
Full product name	BHL 400 X261
Full product code	871150088456500
Order code	913702253112
Material Nr. (12NC)	913702253112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884565
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900067545

HID-Basic BHL for HPL/HPI (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400 X261	6.3 mm	64.0 mm	150.0 mm	135.0 mm	75.0 mm

