



# Dynalite Leading Edge Dimmers

## DLE410

4 channel Leading Edge Dimmer Controller with a maximum load per channel of 10 A.


The Philips Dynalite DLE410 is a four channel leading edge dimmer controller, with a maximum load per channel of 10 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge electronic transformers. - Ideal for applications where multiple user settings are required  
Interference suppression  
Naturally ventilated  
Soft start and voltage regulation technologies  
Diagnostic functionality  
User controls  
Options available

### Product data


| General Information       |   | Order product name              | DLE410        |
|---------------------------|---|---------------------------------|---------------|
| CE mark                   | CE mark   | EAN/UPC – product               | 8710163505268 |
| Remarks                   | Please download the Lighting - Product Data Sheet for more information and ordering options | Order code                      | 50526800      |
| EU RoHS compliant         | Yes   | Numerator – quantity per pack   | 1             |
|                           |   | Numerator – packs per outer box | 1             |
|                           |   | Material no. (12NC)             | 913703006009  |
|                           |   | Net weight (piece)              | 8.450 kg      |
| Application Conditions    |   |                                 |               |
| Ambient temperature range | 0 to +40 °C   |                                 |               |
| Product Data              |   |                                 |               |
| Full product code         | 871016350526800   |                                 |               |

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

