



# Dynalite Leading Edge Dimmers

## DLE1203

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 3 A.


The Philips Dynalite DLE1203 is a 12 channel leading edge dimmer controller, with a maximum load of 3 A per channel and a total device load of 32 A. - It is suitable for use with incandescent, neon and selected fluorescent lighting, as well as iron core and leading edge electronic transformers. - Interference suppression Naturally ventilated Soft start and voltage regulation technologies Diagnostic functionality Options available

### Product data


General Information		Order product name	DLE1203
CE mark	CE mark	EAN/UPC – product	8710163505367
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	913703008009
Application Conditions		Numerator – quantity per pack	1
Ambient temperature range	0 to +40 °C	Numerator – packs per outer box	1
Product Data		Material no. (12NC)	913703008009
Full product code	871016350536700	Net weight (piece)	5.650 kg

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

