



# Dynalite Sensors

## DUS30LHB-D

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

### Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	-5 to +50 °C
Product Data	
Order product name	DUS30LHB-D

Full product name	DUS30LHB-D
Full product code	871869600512500
Order code	913703015609
Material Nr. (12NC)	913703015609
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696005125
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696012628