



Dynalite Sensors

DUS360CS

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871869688796700
CE mark	CE mark	Local code description	DUS360CS
EU RoHS compliant	Yes	Order code	913703243109
		Material Nr. (12NC)	913703243109
		Local order code	.
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696887967
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696894965
Temperature			
Ambient temperature range	32 to +113 °F		
Product Data			
Order product name	DUS360CS		
Full product name	DUS360CS		