



# Dynalite Sensors

## DUS90CS

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

### Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DUS90CS
CE mark	CE mark	Full product code	871869688807000
EU RoHS compliant	Yes	Local code description	DUS90CS
Temperature		Order code	913703244209
Ambient temperature range	-20 to +45 °C	Material Nr. (12NC)	913703244209
Approval and Application		Local order code	.
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8718696888070
Order product name	DUS90CS	Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696895078

## Dynalite Sensors

### Dimensional drawing

