



# Electronic semiparallel ignitor for HID lamp circuits

## **SN 58 T15**

HID ignitors for semi-parallel systems

#### **Product data**


| Operating and Electrical  |                 |  |  |
|---------------------------|-----------------|--|--|
| Input Voltage             | 220 to 240 V    |  |  |
| Line Frequency            | 50 to 60 Hz     |  |  |
| Input Frequency           | 50 to 60 Hz     |  |  |
|                           |                 |  |  |
| Wiring                    |                 |  |  |
| Connector Type            | Screw           |  |  |
|                           |                 |  |  |
| Temperature               |                 |  |  |
| Ambient temperature range | -20 °C to 75 °C |  |  |
| T-Case Maximum (Max)      | 80 °C           |  |  |
|                           |                 |  |  |
| Mechanical and Housing    |                 |  |  |
| Housing                   | Akulon S223     |  |  |
|                           | Akulon S223     |  |  |
|                           |                 |  |  |

| proval Marks CE marking ENEC certificate |
|--|
|  |
|  |
| oduct Data                               |
| der product name SN 58 T15               |
| l product name SN 58 T15                 |
| l product code 697013372879600           |
| der code 913710010413                    |
| terial Nr. (12NC) 913710010413           |
| merator - Quantity Per Pack 1            |
| N/UPC - Product/Case 6970133728796       |
| merator - Packs per outer box 48         |
| N/UPC - Case 6970133728802               |

Datasheet, 2023, April 15 data subject to change

# Electronic semi-parallel ignitor for HID lamp circuits

### Dimensional drawing



| Product   | C1      | A1      | A2      | B1      |
|-----------|---------|---------|---------|---------|
| SN 58 T15 | 38.5 mm | 85.5 mm | 65.0 mm | 41.5 mm |

