PHILIPS Lighting



Electronic semiparallel ignitor for HID lamp circuits

SN 58 T15

HID ignitors for semi-parallel systems

Product data

Operating and Electrical		
Input Voltage	220 to 240 V	
Line Frequency	50 to 60 Hz	
Input Frequency	50 to 60 Hz	
Wiring		
Connector Type	Screw	
Temperature		
Ambient temperature range	-20 °C to 75 °C	
T-Case Maximum (Max)	80 °C	
Mechanical and Housing		

Housing

Akulon S223

Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	SN 58 T15
Full product name	SN 58 T15
Full product code	697013372879600
Order code	913710010413
Material Nr. (12NC)	913710010413
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133728796
Numerator - Packs per outer box	48
EAN/UPC - Case	6970133728802

Electronic semi-parallel ignitor for HID lamp circuits

Dimensional drawing



Product	C1	A1	A2	B1
SN 58 T15	38.5 mm	85.5 mm	65.0 mm	41.5 mm



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, January 16 - data subject to change