



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 427I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BSN 250L 427I TS

Full product name	BSN 250L 427I TS
Full product code	871016306808430
Order code	913710100859
Material Nr. (12NC)	913710100859
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163150482
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163068091

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 427I TS	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm

