



HID-High Power ballasts for MH lamps

BMH 1800L 202

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

General Information	
Application Code	L202
Operating and Electrical	
Input Voltage	230 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Input Current with PF Correction	8.6 A
Input Current without PF Correction	17.3 A
Power Factor without PF Compensation (Max)	0.50
Power Factor without PF Compensation (Min)	0.40
Power Losses (Nom)	75 W
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	1800 W

Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	85 °C
Approval and Application	
Approval Marks	CCC certificate
Product Data	
Full product code	694818229962800
Order product name	BMH 1800L 202
EAN/UPC - Product	6948182295422
Order code	913710107142
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710107142
Net Weight (Piece)	13.500 kg

HID-High Power ballasts for MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 1800L 202	7 mm	102.0 mm	234 mm	185.5 mm	120.0 mm

BMH 1800 L202

