



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 150L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 150L 300I TS	
Input Voltage	220 V	Full product code		697480505007900	
Line Frequency	50 Hz	Order code		913710109142	
Input Frequency	50 Hz	Material Nr. (12NC)		913710109142	
		Numerator - Quantity Per Pack		1	
Wiring		EAN/UPC - Product/Case		6974805050079	
Connector Type	Screw	Numerator - Packs per outer box		6	
		EAN/UPC - Case		6974805050086	
Approval and Application					
Approval Marks	CCC certificate				
Product Data					
Order product name	BSN 150L 300I TS				

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 300I TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

