

# BTA EM ballasts for TL Fluorescent lamps

## BTA 36W 220V C SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.

### Product data

General Information	
Application Code	36W
Design	C
Operating and Electrical	
Input Voltage	220 V
Input Frequency	50 Hz
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Power Factor with PF Compensation	0.85
Power Factor without PF Compensation (Nom)	0.50
Power Losses (Nom)	8.8 W
Wiring	
Wire Striplength	8.0 mm
Ballast Contact Wire Cross Section	0.50-1.00 mm <sup>2</sup>
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	36 W


Temperature	
T-Storage (Max)	80 °C
T-Storage (Min)	-40 °C
T-Winding (Max)	130 °C
Delta-T Normal Conditions	65 °C
Mechanical and Housing	
Housing	L 155x39x28
Approval and Application	
Energy Efficiency Index	C
Approval Marks	CE marking CCC certificate
Product Data	
Full product code	871016306501430
Order product name	BTA 36W 220V C SC
EAN/UPC - Product	8710163149981
Order code	913710119550
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32
Material Nr. (12NC)	913710119550

## BTA EM ballasts for TL Fluorescent lamps

Net Weight (Piece)

0.460 kg

### Dimensional drawing



BTA 36W 220V C 'SC

### Product

BTA 36W 220V C SC

