



# BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

## BPL 26W 240V B2 SC

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.

### Product data


General Information		System characteristics	
Application Code	26W	Rated Ballast-Lamp Power	26 W
Design	B2		
Operating and Electrical		Temperature	
Input Voltage	240 V	T-Storage (Max)	80 °C
Input Frequency	50 Hz	T-Storage (Min)	-40 °C
Mains Voltage Performance (AC)	-8%~+6%	T-Winding (Max)	130 °C
Mains Voltage Safety (AC)	-10%~+10%	Delta-T Normal Conditions	55 °C
Power Factor with PF Compensation	0.85	Mechanical and Housing	
Power Factor without PF Compensation (Nom)	0.45	Housing	L 130x39x28
Power Losses (Nom)	7.3 W		
Wiring		Approval and Application	
Wire Striplength	8.0 mm	Energy Efficiency Index	B2
Ballast Contact Wire Cross Section	0.50-1.00 mm <sup>2</sup>	Approval Marks	CE marking
Connector Type	Screw		
Product Data			
Full product code	871016306562500		
Order product name	BPL 26W 240V B2 SC		
EAN/UPC - Product	8710163150048		

## BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

Order code	913710120550
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32
Material Nr. (12NC)	913710120550

Net Weight (Piece)	0.488 kg
--------------------	----------

### Dimensional drawing



BPL 26W 240V B2 'SC

Product	D1	C1	A1	A2	A3	A4	B1
BPL 26W 240V	4.0 mm	28.0	130.0	115.0	45.0	56.0	39.0
B2 SC		mm	mm	mm	mm	mm	mm

