



Xitanium LED Driver Outdoor Fixed (US)

XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR

Xitanium Outdoor LED Drivers are available in wattages from 40W to 150W for hard-wire integration into outdoor luminaires for the most rugged applications. These drivers operate to specification under wide temperature and electrical ranges to ensure reliability.


Product data

| | |
|-------------------------------------|-----------------|
| General Information | |
| Lighting Technology | LED |
| Operating and Electrical | |
| Line Frequency | 60 Hz |
| Input Frequency | 60 Hz |
| Total Harmonic Distortion IEC (Max) | 20 % |
| Power Consumption | 12.5 W |
| Maximum Efficiency at Full Load | 85 % |
| Output Current (Nom) | 350 mA |
| Input Current (Max) | 100 mA |
| Output Power (Nom) | 10 W |
| Wiring | |
| Connector Type Input Terminals | Wago 250 |
| Output Wire Length | 152.4 mm mm |
| Input Wire Gauge | 18 |
| Temperature | |
| Ambient temperature range | -40 °C to 60 °C |

| | |
|---------------------------------|--|
| T-Case Maximum (Max) | 90 °C |
| Approval and Application | |
| EMI Standard | FCC 47 Subpart 18; Class A |
| Environmental Standard | UL Damp & Dry |
| Approval Marks | RoHS compliance UL certificate CSA certificate |
| Product Data | |
| Full product code | 871016319622000 |
| Order product name | XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR |
| Order code | 913710267302 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 80 |
| Material Nr. (12NC) | 913710267302 |
| Full product name | XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR |
| EAN/UPC - Case | 50781087045157 |
| EAN/UPC - Product/Case | 781087045145 |

Xitanium LED Driver Outdoor Fixed (US)

Dimensional drawing



| Product | D1 | B2 | C1 | C2 | A1 | A2 | B1 |
|----------------|--------|------|------|--------|-------|-------|------|
| XITANIUM 10W | 3.8 mm | 24.6 | 24.9 | 3.0 mm | 132.0 | 122.4 | 34.3 |
| 0.35A 28V 120V | | mm | mm | | mm | mm | mm |
| 60HZ OUTDOOR | | | | | | | |

